

THE FUTURE IS ON®

LEVITON®

LEV Series Pin & Sleeve Devices

IEC 60309-1 & IEC 60309-2

30 Amp Plugs, Connectors,
Inlets & Receptacles

Designed to be more durable and easier to assemble for the most efficient installation and superior performance in any environment.



INDUSTRY
BEST


5
YEAR

WARRANTY

Private labeling capabilities allow for logo customization



No space for debris to build up




Tested to endure impact at the most extreme temperatures

Alternate screwless back clamp assembly option for faster assembly



Standard clamp design includes 2 combination screws

 Plugs & Connectors with Inform™ Technology offer visual power indication for safety


Receptacles and inlets come with **pre-attached gaskets and grounding wires for mounting ease**



Clearly marked **contact carriers** offer quick identification of each wire location



Multiple grommets with **cord diameter ranges molded-in** make it easier to select the correct fit and minimizes the risk of compromising a watertight seal



Captive terminal & assembly screws won't fall out during installation or servicing



LEV Series: North American Configurations

30 A Watertight | Industrial



LEV SERIES

Product Features

- Plugs and connectors constructed of impact modified nylon and receptacles and inlets made of PBT
- Plugs & connectors available with alternate screwless clamp or power indication with Inform technology
- Nickel-plated brass pins and sleeves for added corrosion-resistance
- Watertight and dust-tight rated to IP66, IP67, IP68 and IP69K
- Listed to UL 1682 and 1686, CSA and NOM-ANCE requirements, CE Marked
- NSF certified sanitary design trusted for use in food & beverage facilities
- Meets North American IEC 60309-1 and 60309-2 standards
- Backed by an industry best 5-year warranty



30 A Watertight Pin & Sleeve Devices Accessories available at leviton.com/LEVseries

Wiring	Color	Voltage AC	Connector/ Receptacle Clock Position	Plug/ Inlet View	HP Rating	Plug w/Standard Clamp	Plug w/ Alternate Screwless Clamp	Connector w/Standard Clamp	Connector w/ Alternate Screwless Clamp	Receptacle	Inlet
2p3w	Yellow	125	4		NA	330P4WLEV	330P4WLEVA	330C4WLEV	330C4WLEVA	330R4WLEV	330B4WLEV
	Blue	250	6		NA	330P6WLEV	330P6WLEVA	330C6WLEV	330C6WLEVA	330R6WLEV	330B6WLEV
	Red	480	7		NA	330P7WLEV	330P7WLEVA	330C7WLEV	330C7WLEVA	330R7WLEV	330B7WLEV
3p4w	Orange	125/250	12		NA	430P12WLEV	430P12WLEVA	430C12WLEV	430C12WLEVA	430R12WLEV	430B12WLEV
	Blue	3Ø250	9		7.5	430P9WLEV*	430P9WLEVA**	430C9WLEV*	430C9WLEVA**	430R9WLEV	430B9WLEV
	Red	3Ø480	7		15	430P7WLEV*	430P7WLEVA**	430C7WLEV*	430C7WLEVA**	430R7WLEV	430B7WLEV
	Black	3Ø600	5		20	430P5WLEV	430P5WLEVA	430C5WLEV	430C5WLEVA	430R5WLEV	430B5WLEV
4p5w	Blue	3ØY120/208	9		5	530P9WLEV	530P9WLEVA	530C9WLEV	530C9WLEVA	530R9WLEV	530B9WLEV
	Red	3ØY277/480	7		15	530P7WLEV	530P7WLEVA	530C7WLEV	530C7WLEVA	530R7WLEV	530B7WLEV
	Black	3ØY347/600	5		20	530P5WLEV	530P5WLEVA	530C5WLEV	530C5WLEVA	530R5WLEV	530B5WLEV



Custom configurations available upon request.

* Add "PI" to end of part number for Power Indication

** Change to "PIA" for Power Indication and Alternate Screwless Clamp


Standard Clamp



Alternate Screwless Clamp

Withstands any wet and harsh location with the highest and most comprehensive ratings on the market

IP66, IP67, IP68 & IP69K





Enabling conventional Leviton products to provide real-time information that is used to improve operational safety, efficiency, and productivity.



Inform™ Technology allows users to:

**IMPROVE
SAFETY & EFFICIENCY**

by monitoring the quality and performance of the devices

**MINIMIZE
UNPLANNED DOWNTIME**

by alerting end-users of potential problems with real-time information

**MAXIMIZE
PRODUCTIVITY**

by contributing to overall predictive maintenance schemes

Learn more at leviton.com/inform

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line (8:30AM-7:00PM E.S.T. Monday-Friday): 1-800-824-3005

Visit our Website at: www.leviton.com/LEVseries • email: industrial@leviton.com

© 2019 Leviton Manufacturing Co., Inc. All rights reserved. Specifications subject to change without notice.

Q-1199